
# CO2 LASERS \ Air & Water-Cooled

# **ULR-60**

#### **▼ FEATURES**

- · Air and water-cooled options
- · Integrated RF supply
- · Temperature warning output
- Temperature cutoff to prevent damage to laser
- · Fault indicator LED
- Low profile mounting plate
- · Excellent power stability
- · Quiet operation
- Ability to retrofit to current 60-watt CO<sub>2</sub> installations
- Manufactured with proven ULS technology
- Class IV configurations available
- RoHS compliant



### LASER SPECIFICATIONS<sup>\*</sup> ¥

Rated Power**	60 W
Wavelength	10.6μm
Power Stability	±5% after 15 minutes of CW operation
M <sup>2</sup>	1.3 ± 0.2
Beam Size (Near Field) <sup>†</sup>	4 ± 1mm
Beam Divergence (Full Angle)	5 ± 1 mrad
Polarization	Linear
Pointing Stability	200 μrad
Optical Pulse Rise or Fall Time	120 ± 40 μs
Optical Delay Time	38 ± 10 μs
Optical Modulation	100% up to 5KHz
Modulation Signal Type	0-5 VDC

#### LASER SPECIFICATIONS\*


Cooling	Integrated Air/Water
Weight (Air-cooled)	28 lbs (12.7 kg) - Class IV
	21 lbs (9.5 kg) - OEM
Dimensions	see rear panel
Environmental	
Ambient Temperature <sup>††</sup>	50-95°F (10-35°C)
Relative Humidity	<90% (non-condensing)
Power Requirements	
DC Input Voltage	48 VDC
RMS Current (CW, with fan)	20 A

<sup>\*</sup> These specifications are subject to change without notice. \*\* Output power is guaranteed to exceed this level for the duration of ULS warranty regardless of use. † Near field approximately 150mm from output coupler. †† At temperatures below 50°F [10°C] operation may be intermittent and there is a potential for damage to the power supply and optics.


www.co2laser.com



## ➤ BASIC CONFIGURATION (WATER-COOLED SHOWN BELOW)



#### **▼ INTEGRATED COOLING/CLASS IV CONFIGURATIONS (CLASS IV AIR-COOLED SHOWN BELOW)**



These OEM lasers are components intended for integration into OEM equipment and as such do not comply with the Federal regulations (21 CFR Subchapter J) as administered by the Center for Devices and Radiological Health. Purchaser acknowledges that it is his responsibility to obtain compliance with all CDRH and other applicable domestic and/or international safety standards. Protected under U.S. patents 5,661,746; 5,754,575; 5,867,517; 5,881,087; 5,894,493; 5,901,167; 5,982,803; 6,181,719; 6,983,001. Other U.S. and international patents pending. ©2008 All rights reserved. Universal Laser Systems logo and name are registered trademarks of Universal Laser Systems, Inc.

WARNING: UNIVERSAL LASER SYSTEMS PRODUCTS ARE NOT DESIGNED, TESTED, INTENDED OR AUTHORIZED FOR USE IN ANY MEDICAL APPLICATIONS, SURGICAL APPLICATIONS, MEDICAL DEVICE MANU-FACTURING, OR ANY SIMILAR PROCEDURE OR PROCESS REQUIRING APPROVAL, TESTING, OR CERTIFICATION BY THE UNITED STATES FOOD AND DRUG ADMINISTRATION OR OTHER SIMILAR GOVERNMENTAL. ENTITIES. SHOULD THE BUYER USE UNIVERSAL LASER SYSTEMS PRODUCTS OR ANY SUCH UNINITENDED OR UNAUTHORIZED APPLICATION, ALL WARRANTIES REGARDING THE UNIVERSAL LASER SYSTEMS PRODUCTS SHALL BE NULL AND VOID. FURTHER, THE BUYER SHALL HAVE NO REMEDY AGAINST UNIVERSAL LASER SYSTEMS AND ITS OFFICERS, EMPLOYEES, SUBSIDIARIES, AFFILIATES AND DISTRIBUTORS FOR, AND THE BUYER SHALL INDEMNIFY AND HOLD THOSE PARTIES HARMLESS AGAINST, ANY AND ALL CLAIMS, COSTS, DAMAGES, EXPENSES AND REASONABLE ATTORNEY FEES ARISING OUT OF, DIRECTLY, OR INDIRECTLY, ANY CLAIM ASSOCIATED WITH SUCH UNINTENDED OR UNAUTHORIZED USE, INCLUDING BUT NOT LIMITED TO ANY CLAIM BASED ON WARRANTY (EXPRESS OR IMPLIED), CONTRACT, TORT (INCLUDING ACTIVE, PASSIVE, OR IMPUTED NEGLIGENCE), STRICT LIABILITY, PATENT OR COPYRIGHT INFRINGEMENT OR MISAPPROPRIATION OF INTELECTULA PROPERTY.